

809 Xispal RS Tubular

Rev. 3

Uso recomendado /
Recommended end-use:
PUÑOS / CUFFS

Composición / Composition:
54% Acrílica modificada tipo-F / Modified acrylic fibre type-F
35% Algodón / Cotton
9,5% Viscosa / Viscose
1,5% Antiestático / Antistatic



809 Xispal RS Tubular

LIGAMENTO / LIGAMENT	Canalé / Rib Knit		
PESO / WEIGHT (gr/m)	90 ± 5%	UNE 40339	
ANCHO / WIDTH (cm)	8 ± 1 Tubular		
PRETRATAMIENTO / PRE-TREATMENT	Standard requirement	50 washes	
INFLAMABILIDAD INFLAMABILITY	A1 - A2	A1 - A2	EN 15025 (EN 11612)
RESISTENCIA AL CALOR HEAT RESISTANCE	Pass	Pass	ISO 17493 (EN 11612)
ANTIESTÁTICO / ANTISTATIC	Pass	Pass	EN 1149/3/5
ALTA VISIBILIDAD / HIGH VISIBILITY <i>(opcional)</i>	Pass ¹	Not tested	EN 20471

¹Condiciones de lavado EN 6330 (60°C) / Washing instructions EN 6330 (60°C)

809 Xispal RS Tubular

Rev. 3

Sectores recomendados / Recommended use:

COMPLEMENTO DE CONFECCIÓN / / MANUFACTURED COMPLEMENT

Normativas para prenda / Standard for garments:



Instrucciones de lavado EN 15797 (75°C) / Washing instructions EN 15797 (75°C):



*Evitar utilizar suavizantes / Avoid using softeners

Colores disponibles / Available colors:



Naranja 20
Orange 20



Gris 80
Grey 80



Marino 60
Navy Blue 60